

Baby scale KERN MBB

APPROVED MEDICAL DEVICE



Baby scale – with EC type approval class III and approval for professional mobile or stationary medical use in medical diagnostics

Features

- Verification class III (verification is optional)
- Approved as a medical device according to 93/42/EEC
- Large, ergonomically optimised tray for safe weighing of neonates
- Removable tray enables use as a scale for infants as well
- Robust ABS plastic. For easy and hygienic cleaning
- Secure and non-slip positioning with height-adjustable rubber feet
- Level indicator to level the balance precisely
- Hold function:
When patients do not stand or lie completely still, a stable weight is calculated using an average weight and this is then “frozen”. This means that you have sufficient time to attend to the young patient first and then take the weight reading in peace
- Wall mount for display device
- Battery- or mains-powered, rechargeable battery operation optional


Technical data

- LCD display, digit height 25 mm
- Dimensions of tray
W×D 550×240 mm
- Dimensions of weighing plate
W×D×H 250×250×70 mm
- Dimensions of display device
W×D×H 210×110×50 mm
- Overall dimensions
W×D×H 560×288×136 mm
- Cable length of display device approx. 50 cm
- Battery operation possible, 6×1,5 V AA, not included, operating time up to 120 h
- Mains adapter external, included
- Net weight approx. 4 kg

Accessories

- Carrying case for mobile use, KERN MBB-A02
- Stand to elevate display device, height of stand approx. 450 mm, KERN EOB-A01
- Protective working cover over the display device, standard, can be reordered, scope of delivery: 5 items, KERN EOB-A02S05
- Cleaning cloths, alcohol-free cloths for wipe disinfectant, quick-acting, on basis of modern quaternary ammonium compounds, and also against papova viruses. Particularly gentle on materials, and therefore very well suited for the disinfection of alcohol sensitive medical products. Fulfill the legal requirements for occupational safety in accordance with TRGS 525/540. Packaging contents 80 pcs., size 20×22 cm per cloth KERN MYC-01
- Internal rechargeable battery pack, operating time up to 50 h, charging time approx. 24 h, KERN FOB-A08

STANDARD



OPTION



FACTORY



* Within the EU, official verification is mandatory by law for scales that are intended for use as a medical device. Please add this to your order. We require the location of use and the post code for the verification.

Model	Weighing range	Readability	Verification value	Mandatory by law Verification	
				KERN	
KERN MBB 15K2DM	[Max] kg 6 15	[d] kg 0,002 0,005	[e] kg 0,005	965-128.	

Pictograms

<p>Adjusting program CAL: For quick setting up of the balance's accuracy. External adjusting weight required.</p>	<p>Hold function: When the weighing conditions are unstable, a stable weight is calculated as an average value.</p>	<p>Binocular Microscope: For the inspection with both eyes</p>
<p>Data interface RS-232: To connect the balance to a printer, PC or network.</p>	<p>Protection against dust and water splashes IPxx: The type of protection is shown in the pictogram.</p>	<p>Trinocular Microscope: For the inspection with both eyes and the additional option for the connection of a camera</p>
<p>RS-485 data interface: To connect the balance to a printer, PC or other peripherals. Suitable for data transfer over large distances. Network in bus topology is possible</p>	<p>Stainless steel: The balance is protected against corrosion.</p>	<p>Abbe Condenser: With high numerical aperture for the concentration and the focusing of light.</p>
<p>Bluetooth* data interface: To transfer data from the balance to a printer, PC or other peripherals.</p>	<p>Suspended weighing: Load support with hook on the underside of the balance.</p>	<p>Halogen illumination: For pictures bright and rich in contrast.</p>
<p>Control outputs (optocoupler, digital I/O): To connect relays, signal lamps, valves, etc.</p>	<p>Battery operation: Ready for battery operation. The battery type is specified for each device.</p>	<p>LED illumination: Cold, energy saving and especially long-life illumination.</p>
<p>Statistics: using the saved values, the device calculates statistical data, such as average value, standard deviation etc.</p>	<p>Rechargeable battery pack: Rechargeable set.</p>	<p>Fluorescence illumination for compound microscopes: With 100W mercury lamp and filter.</p>
<p>PC Software: to transfer the measurements from the device to a PC.</p>	<p>Battery operation rechargeable: Prepared for a rechargeable battery operation</p>	<p>Fluorescence illumination for compound microscopes: With 3W LED illumination and filter.</p>
<p>GLP/ISO-Protokoll: With date and time. Only with KERN printers.</p>	<p>Universal mains adapter: with universal input and optional input socket adapters for A) EU, CH B) EU, CH, GB, USA</p>	<p>Phase contrast unit: For a higher contrast.</p>
<p>Piece counting: Reference quantities selectable. Display can be switched from piece to weight.</p>	<p>Mains adapter: 230V/50Hz in standard version for EU. On request GB, AUS or USA version available.</p>	<p>Darkfield condenser/unit: For a higher contrast due to indirect illumination</p>
<p>Totalising level A: The weights of similar items can be added together and the total can be printed out.</p>	<p>Power supply: Integrated in balance. 230V/50Hz standard EU. More standards e.g. GB, AUS or USA on request.</p>	<p>Polarising unit: To polarise the light.</p>
<p>Weighing units: Can be switched to e.g. nonmetric units at the touch of a key. Please refer to website for more details.</p>	<p>Weighing principle: Strain gauges Electrical resistor on an elastic deforming body.</p>	<p>Infinity system: Infinity corrected optical system.</p>
<p>Weighing with tolerance range: (Check weighing) Upper and lower limiting can be programmed individually, e.g. for sorting and dosing. The process is supported by an audible or visual signal, see the relevant model</p>	<p>Peak hold function: capturing a peak value within a measuring process.</p>	<p>Automatic temperature compensation: For measurements between 10 °C and 30 °C</p>
<p>Hold function: When patients do not stand, sit or lie completely still, a stable weight is calculated using an average weight.</p>	<p>Push and Pull: the measuring device can capture tension and compression forces.</p>	<p>Verification possible: The time required for verification is specified in the pictogram.</p>
<p>Integrated scale: In the eyepiece.</p>	<p>360° rotatable microscope head</p>	<p>Package shipment: The time required for internal shipping preparations is shown in days in the pictogram.</p>
<p>Monocular Microscope: For the inspection with one eye.</p>	<p>Pallet shipment: The time required for internal shipping preparations is shown in days in the pictogram.</p>	

*The Bluetooth® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by KERN & SOHN GmbH is under license. Other trademarks and trade names are those of their respective owners.

Your KERN specialist dealer

Impex Produkter AS
Gamle Drammensvei 107
1363 Høvik
www.impex.no

info@impex.no
Tel.: 22 32 77 20