

Digital Pocket Refractometer PAL-COFFEE (BX/TDS)



PAL-COFFEE(Dual sale of Brix and TDS), which famous Baristas are using for their important tools, has the high resolution of 0.01%. The subtle difference in the concentration of coffee and espresso can be measured. Stable readings are possible even with high-temperature, fresh brew due to the continuous measurement feature.

For Brix scale, please choose PAL-Coffee(Brix). For TDS scale, pleas choose PAL-Coffee(TDS).

## Specifications

Model	PAL-COFFEE (BX/TDS)
Cat.No.	4533
Scale	Brix Todal Dissolved Solids(TDS)
Range	Brix: 0.00 to 25.00% TDS: 0.00 to 22.00%
Resolution	Brix: 0.01% TDS: 0.01%
Accuracy	Brix: ±0.10% TDS: ±0.15%
Temperature compensation	10 to 100°C

## Accessories

· PAL-CASE : RE-39409

· JORDAN for PAL(Silicon Cover): RE-39414

· STRAP: RE-39410

· Battery Case Cover With O-Ring : RE-38048

 $\cdot \text{ USB Battery Charger}: RE\text{-}34801 \\ \cdot 20\% \text{ Sucrose } (\pm 0.03\%): RE\text{-}110020$ 

