Stereo zoom microscope KERN OZL-46







OZL 465 With ring illumination



OZL 467 With handle

LAB LINE

The flexible, affordable all-rounder with zoom function for schools, training companies, inspection authorities and laboratories

Features

- The products in the KERN OZL-46 series are stereo zoom microscopes, which will impress you with their quality, easy handling, flexibility as well as their stability and economical price
- The LED reflected and transmitted illumination included as standard guarantees the very best illumination of your sample
- The highlight of the OZL 465/OZL 466 is the strong, continuously dimmable, integrated LED ring illumination in the objective housing, which ensures uniform, shadow-free illumination. An LED transmitted light variant is also included
- As well as excellent optical characteristics and their large working surface, these models offer the highest level of comfort in this class – ideal for training companies, workshops as well as assembly and repair workstations, e.g. in the electronics industry
- The zoom objective offers you continuous magnification from 7×-45×

- The KERN OZL-46 series is available as a binocular or trinocular version
- The pillar stand offers you the highest level of flexibility and the freedom to remove the microscope head and to integrate it into other modular systems, for example into a universal stand
- With its integrated handle as well as its stable arm curved stand, the KERN OZL 467/ OZL 468 has been specially developed for schools and workshops
- A large selection of eyepieces, external illumination units as well as auxiliary objectives are available as accessories
- A protective dust cover, eye cups, as well as multi-lingual user instructions are included in the scope of delivery
- A C-mount adapter is required to connect a camera to the trinocular version. You can select this adapter from the following model outfit list
- Please find detailed information in the following model outfit list

Scope of application

 In vitro fertilisation, detection of parasites, zoology and botany, tissue preparation, section, quality control

Applications/Samples

 Samples with focus on three-dimensional impression, zoom with variable magnification (depth, thickness), e.g. insects, seeds, circuit boards, components

Technical data

- Optical system: Greenough optics
- Brightness adjustable (separate)
- Tube 45° inclined
- Magnification ratio: 6,4:1
- Light distribution 50:50
- Interpupillary distance 55 75 mm
- Diopter adjustment: Both-sided
- Overall dimensions W×D×H 300×240×420 mm
- · Net weight approx. 4 kg

STANDARD



Model	Standard configuration						
	Tube	Eyepiece	Field of view	Objective	Stand	Illumination	
KERN			mm	Zoom			
OZL 463	Binocular	HWF 10×/Ø 20 mm	Ø 28,6 – 4,4	0,7×-4,5×	Pillar style	3 W LED (incident); 3 W LED (transmitted)	
OZL 464	Trinocular	HWF 10×/Ø 20 mm	Ø 28,6 – 4,4	0,7×-4,5×	Pillar style	3 W LED (incident); 3 W LED (transmitted)	
OZL 465	Binocular	HWF 10×/Ø 20 mm	Ø 28,6 - 4,4	0,7×-4,5×	Pillar style	3 W LED (incident); 3 W LED (transmitted)	
OZL 466	Trinocular	HWF 10×/Ø 20 mm	Ø 28,6 - 4,4	0,7×-4,5×	Pillar style	3 W LED (incident); 3 W LED (transmitted)	
OZL 467	Binocular	HWF 10×/Ø 20 mm	Ø 28,6 - 4,4	0,7×-4,5×	Arm curved	3 W LED (incident); 3 W LED (transmitted)	
OZL 468	Trinocular	HWF 10×/Ø 20 mm	Ø 28,6 - 4,4	0,7×-4,5×	Arm curved	3 W LED (incident); 3 W LED (transmitted)	



Stereo zoom microscope KERN OZL-46

Eyepiece	Specifications - Objectives											
	Magnification	Standard	Auxiliary objectives									
		1,0×	0,5×	0,75×	1,5×	2,0×						
HSWF 10×	Total magnification	7×-45×	3,5×-22,5×	5,3×-33,8×	10,5×-67,5×	14× - 90×						
	Field of view mm	Ø 28,6 - 4,4	ø 57,1 – 8,9	Ø 38,1 – 5,9	Ø 19 - 3	Ø 14,3 - 2,2						
HWF 15×	Total magnification	10,5× - 67,5×	5,3×-33,8×	7,9×-50,6×	15,5× - 101,3×	21× - 135×						
	Field of view mm	Ø 21,4 - 3,3	Ø 42,9 - 6,7	Ø 28,5 - 4,4	Ø 14,3 - 2,2	Ø 10,7 - 1,7						
HSWF 20×	Total magnification	14× - 90×	7× - 45×	10,5×-67,5×	21× - 135×	28× - 180×						
	Field of view mm	Ø 14,3 - 2,2	Ø 28,6 - 4,4	Ø 19,1-2,9	Ø 9,5 - 1,5	Ø 7,1 – 1,1						
LIME 05	Total magnification	17,5× - 112,5×	8,8×-56,3×	13,1×-91,9×	26,3× - 168,8×	35× - 225×						
HWF 25×	Field of view mm	Ø 12,9 – 2,0	Ø 25,7 – 4,0	Ø 17,2 - 2,7	Ø 8,6 - 1,3	Ø 6,4 - 1,0						
Working distance		105 mm	177 mm	120 mm	47 mm	26 mm						
Maximum sample height		140 mm	35 mm	80 mm	165 mm	185 mm						

Model outfit				Model	KERN		Order number		
		OZL 463	OZL 464	OZL 465	OZL 466	OZL 467	OZL 468		
Eyepieces (30,0 mm)	HWF 10×/ø 20 mm	11	11	11	11	11	11	OZB-A4631	
	HSWF 15×/Ø 15 mm	00	00	00	00	00	00	OZB-A4632	
	HWF 20×/ø 10 mm	00	00	00	00	00	00	OZB-A4633	
	HSWF 25×/ø 9 mm	00	00	00	00	00	00	OZB-A4634	
	0,5×	0	0			0	0	OZB-A4641	
	0,75×	0	0			0	0	OZB-A4644	
Auxiliary objectives	1,5×	0	0			0	0	OZB-A4642	
	2,0×	0	0			0	0	OZB-A4643	
	Soldering protection lens	0	0			0	0	OZB-A4645	
C-Mount	1× (focus adjustable)		✓		✓		1	OZB-A4809	
	0,3× (focus adjustable)		0		0		0	OZB-A4810	
	0,5× (focus adjustable)		0		0		0	OZB-A4811	
Eyepiece camera adapter	1,0×; for fitting an eyepiece camera to the trinocular connection of the microscope		0		0		0	OZB-A4863	
Stand	Pillar style, with 3 W-LED illumination (transmitted + incident)	1	1						
	Pillar style, with 3 W-LED illumination (transmitted)			1	✓				
	Arm curved, incl. handle, with 3 W-LED illumination (transmitted + incident)					~	1		
Ring illumination	Integrated into the microscope head as incident illumination			~	~				
Stage plate	Frosted glass/Ø 95 mm	1	✓	✓	✓	✓	1	OZB-A4670	
	Black-white/Ø 95 mm	1	✓	✓	✓	✓	1	OZB-A4806	
External illumination	Please find the information about external illumination units in the catalogue on page 83 and on the internet ✓ = Included with delivery O = Opti								

✓ = Included with delivery

O = Option

USB 3.0 digital camera

WLAN data interface

mobile display device

HDMI digital camera

To transfer the measurements

For measurements between

10 °C and 30 °C

Battery operation

Plug-in power supply

operation

Automatic temperature compesation

Protection against dust and water splashes

IPxx: The type of protection is shown in the

Ready for battery operation. The battery

type is specified for each device.

Battery operation rechargeable

Prepared for a rechargeable battery

230V/50Hz in standard version for EU.

On request GB, AUS or USA version.

Integrated power supply unit Integrated in microscope. 230V/50Hz

standard EU. More standards e.g. GB, AUS or USA on request.

pictogram cf. DIN EN 60529:2000-09, IEC 60529:1989+A1:1999+A2:2013

from the device to a PC

PC software

For transmitting of the picture to a

USB 3.0

HDMI

AUTO

ATC

ΙP

■→

230 V

For direct transmitting of the picture to a PC

For direct transmitting of the picture to a display

Pictograms



360° rotatable microscope head





Monocular Microscope

For the inspection with one eye



Binocular Microscope

For the inspection with both eyes



Trinocular Microscope

For the inspection with both eyes and the additional option for the connection of a camera



Abbe Condenser

With high numerical aperture for the concentration and the focusing of light



Halogen illumination

For pictures bright and rich in contrast



LED illumination

Cold, energy-saving and especially long-life illumination



Incident illumination

For non-transparent objects



Transmitting illumination

For transparent objects



Fluorescence illumination

For stereomicroscopes




Fluorescence illumination for compound microscopes

With 100W mercury lamp and filter



For direct transmitting of the picture to a PC

Fluorescence illumination for compound microscopes





Phase contrast unit

For a higher contrast



Darkfield condenser/unit

For a higher contrast due to indirect illumination



Polarising unit

To polarise the light



Infinity system

Infinity corrected optical system



Zoom magnification For stereomicroscopes



Auto-focus

For automatic control of the focus level



Parallel optical system

For stereomicroscopes, enables fatigue-proof working



Integrated scale

In the eyepiece



SD card





USB 2.0 digital camera



Package shipment

The time required to manufacture the product internally is shown in days in the pictogram.

Abbreviations

Adapter for the connection of a C-Mount

camera to a trinocular microscope

High (Super) Wide Field (Eyepiece with

high eye point for wearers of glasses)

Long Working Distance

SWF

Super Wide Field (Field number at least Ø 23 mm for 10× eyepiece)

Working Distance W.D.

FPS

H(S)WF

Frames per second

N.A.

SLR

LWD

Numerical Aperture Single-Lens Reflex camera

WF

Wide Field (Field number up to Ø 22 mm for 10× eyepiece)

Your KERN specialist dealer:

Impex Produkter AS Gamle Drammensvei 107 1363 Høvik www.impex.no info@impex.no Tel.: 22 32 77 20