



More information on the website
radwag.com/en/info,w1,MIA

UYA 2.5Y.F Ultra-Microbalance

WL-109-0003



The drawings, photos and graphics used are for illustrative purposes only.

Functions



Autotest



Percent Weighing



Peak hold



Statistics



IR sensors



GLP Procedures



Air density correction



Moveable range



Differential weighing



Ambient conditions monitoring



Replaceable unit



Statistical Quality Control



ALIBI Memory



Wi-Fi

Datasheet

Metrological parameters	
Maximum capacity [Max]	2.1 g
Minimum load	0.01 mg
Readability [d]	0.1 µg
Verification unit [e]	1 mg
Tare range	-2.1 g
Minimum weight (USP)	0.3 mg

Metrological parameters	
Minimum weight (U=1%, k=2)	0.03 mg
Standard repeatability [Max]	0.35 µg
Standard repeatability [5% Max]	0.15 µg
Permissible repeatability [Max]	0.6 µg
Permissible repeatability [5% Max]	0.35 µg
Linearity	±1.5 µg
Eccentric load deviation	1.5 µg
Sensitivity time drift	1×10 ⁻⁶ /Year×Rt
Stabilization time	4 – 12 s
Adjustment	internal (automatic)
OIML Class	I
Physical parameters	
Leveling system	automatic – Reflex Level System
Display	10" graphic colour touchscreen
Delivery components	Ultra-microbalance, terminal, weighing pan, weighing pan for filters, centring ring, glass lid, pincette, brush, fabric dust cover.
Weighing chamber dimensions	ø 93.8×35 mm
Weighing pan dimensions	ø70 + ø16 mm
Anti-draft chamber dimensions	560×350×252 mm
Packaging dimensions W x D x H	750×492×595 mm
Net weight	10.6 kg
Gross weight	16.5 kg
Construction	
Protection class	IP 43
Communication interface	
Communication interface	2×USB-A, USB-C, RS 232 (COM3), HDMI, Ethernet, Wi-Fi, Hotspot
Electrical parameters	
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A Max; 15V DC 2.4A Balance: 12 – 15V DC 1.4A max; 9 – 17W*
Environmental conditions	
Operating temperature	+10 – +40 °C
Operating temperature change rate	±0.3 °C / 1 h (±1 °C / 8 h)
Relative humidity	40% – 80%
Relative humidity change rate	±1% / h (±4% / 8 h)

Repeatability is expressed as a standard deviation from 10 cycles of mass standard weighing.

Stabilization time dependson the ambient conditions and the dynamics of weighing pan loading; specified for FAST profile.

* Power consumption depends on the terminal configuration as well as the number and type of external devices connected.

The power supply can be connected to the socket on the back of the balance housing or to the terminal.

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Additional fee for verification



Accessories (Additional Fee)

MediaBox
RFID Tags
Antivibration Tables
Power Adapters
Additional modules
Professional Weighing Tables
Antistatic ionizer

Protective cover for balances
Barcode scanners
RS 232, RS 485 cables
Label Printers
THBR 2.0 System - Ambient Conditions Monitoring
Receipt Printer
Fingerprint Reader

Software (Additional Fee)

- E2R Weighing [WX-010-0099]
- Label Editor R02 [WX-010-0094]
- R-Lab [WX-010-0080]
- RADWAG Development Studio [WX-010-0104]

- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]
- Scale Editor 2.1 [WX-010-0173]

Device dimensions W x D x H

